

TECHNICAL DATA SHEET

BV-300 Type 5-B/6-B Protective Coverall

BV-300 Type 5B-6B Protective Coveralls provide protection against hazardous dusts (Type 5) and light liquid splashes (Type 6).



www.bellevitae.com

KEY FEATURES

- Single-use coveralls
- Provides preliminary protection against dust particles and light liquid splashes.
- Flexible waist, ankle and wrist areas provide convenience and movement freedom while preserving a comfortable and tight fit.
- Front zipper with cover flap for easier dressing without compromising protection
- Anti-static coating and low linting, breathable fabric.
- Anti-static treatment help reduce static build-up.
- Non-sterile
- Offers protection against biohazard

APPROVALS AND PROTECTION

EN ISO 13982-1: 2004/A1:2010



EN 14126: 2003/AC:2004



EN 1149-5:2018



Fulfill the requirements for Category III PPE. CE approved under Personal Protective Equipment Regulations, (EU) 2016/425

APPLICATIONS

Typical applications may include asbestos inspection, coal dust in power plants, metal polishing, light-duty building cleaning, machine or vehicle maintenance, paint spraying, pharmaceutical, general industrial clean-up, insulation laying, woodworking, general powder handling, food processing, blood, bodily fluids, and environmentally controlled clean room applications. For further information on products and its areas of usage, please contact BelleVitae representatives

info@bellevitae.com Phone: +90 0212 706 1003



SIZE

An appropriate size for the garment should be selected to allow sufficient movement for the wearer whilst maintaining a secure fit.



	SIZE CHART	
SIZE	HEIGHT	CHEST
s	163-169 cm	97-104 cm
М	169-177 cm	104-112 cm
L	177-184 cm	112-120 cm
XL	184-192 cm	120-128 cm
XXL	192-199 cm	128-136 cm
3XL	199-207 cm	136-144 cm

MATERIALS	
SUIT	Microporous polyethylene laminate nonwoven
WEIGHT	40±3gsm
ZIPPER	Polyester Braid
THREAD	Polyester

LIMITED USE













Do not





Do not tumble dry

Flammable

STORAGE AND DISPOSAL

- Store within the temperature range -5°C to +25°C and with the relative humidity below %80
 - Store in dry, clean conditions in original packaging away from solvent vapours.
 - Care should be taken when removing contaminated garments, so as not to contaminate the user with any hazardous substances. If garments are contaminated, then decontamination procedures should be followed prior to removal of the garment.
 - Handle and dispose of contaminated garments with care in accordance with applicable local regulations.
 - Expected shelf life is five years from date of manufacture when stored as stated.

WARNING AND LIMITATIONS

Make sure that the product is suitable for the application and fitted correctly. Product must never be altered or modified. Final determination as to the suitability of these products for a particular situation is the employer's responsibility. Electrostatic Dissipative (ESD) Protective clothing shall not be opened or removed whilst in presence of flammable or explosive atmospheres or while handling flammable or explosive substances. This information is subject to revision at any time.

PACKAGING

Each coverall is individually folded and packaged into a bag.

Phone: +90 0212 706 1003